



WORLDWIDE LEADER OF SOURCE SAMPLING EQUIPMENT

## ▶ **Compact Method 5 Sampling Kit** Independently Heated Stainless-Steel Filter Assembly




The compact Method 5 kit does not require a separate heated filter compartment and utilizes a flexible sample line and a split umbilical cord with a power adapter to allow sampling in space-limited areas.

**Scan the QR Code for  
More Information**


### Features

- Independently heated stainless steel filter assembly (SFA-82H) that connects directly to a standard Method 5 probe
- Flexible sample line and a split umbilical cord with a power adapter to allow sampling in space-limited areas
- Standard glass impingers have been replaced with stainless steel impingers (SN-5CREVA) to eliminate glass breakage
- Three filter assemblies are recommended to speed up the turnaround time between consecutive runs. All applicable components are rated 120 V at 60 Hz




## ► Compact Method 5 Sampling Kit Part # SK-CM5-\_ Packing List

### Heated Filter Assembly



**Your Method 5 Sampling Solution**



**SCAN THE QR CODE  
FOR THE COMPLETE PACKING LIST**